
28" ENCLOSURE WITH KNOCKOUTS (NO COVER)

EN2885 | [On-Q](#)



FEATURES & BENEFITS

The EN2085 series enclosures include five knockouts on the top of the enclosure. They are also vertically stackable to allow cable passthrough between any two ENxx85 enclosures. For Fiber to the Home (FTTH) applications, it will fit ONTs of 3.6" depth or less.



- Includes five openings on the top of the enclosure with knockouts
- Stackable design allows for connection of two systems
- Cover not included
- In FTTH applications, it fits ONTs of 3.6" depth or less. In 28" and 42" enclosures, 2.5" can be added to depth with enclosure extender
- UL listed
- Made in the USA

SPECIFICATIONS

GENERAL INFO

Color: Glossy White
Finish: Powder Coat
Type: Enclosure

LISTING AGENCIES/THIRD PARTY CERTIFICATIONS

RoHS: Yes
CSA Listing Info: CSA-C22.2 No. 144.1 (2006), CAN/CSA-C22.2 No. 182.4-1990
CSA Standard: Yes
cULus: Yes
UL Listing No: ANSI/UL 1863, ANSI/UL 985, ULC-S545, ANSI/UL 1023
UL Standard: Yes

UN SPSC: 43223306

CONSTRUCTION INFORMATION

Installation Location: In-Wall

DIMENSIONS

Depth (Metric): 9.4 cm

Depth (US): 3.7"

Height (Metric): 71.4 cm

Height (US): 28.1"

Width (Metric): 36.3 cm

Width (US): 14.3 in

Thickness (US): 20 Gauge

TECHNICAL INFORMATION

Humidity: 90% Relative Humidity (Non-Condensing)

Material: CRS

Mounting: Surface or Flush

Operating Temperature (Celsius): 0°C to 50°C