
42" ENCLOSURE (NO COVER)

EN4280 | [On-Q](#)

FEATURES & BENEFITS

Perfect for larger installations, this 42" enclosure features universal On-Q style mounting holes that are compatible with all bay-style modules. It also includes larger top openings that make pulling wire easier as well as additional knockouts, more side lances, and side tabs for more flexible mounting.



- Flanged covers hide drywall openings
- Drywall depth indicators
- Flush and surface installation
- Mounting tabs provide correct flush-mount position for standard installations
- Patented mounting system offers versatile module mounting options
- Literature pouch included for dealer information
- Includes self-adhesive cable identification table
- Made in the USA

SPECIFICATIONS

GENERAL INFO

Color: Glossy White
Finish: Powder Coat
Type: Enclosure

LISTING AGENCIES/THIRD PARTY CERTIFICATIONS

RoHS: Yes
CSA Listing Info: CSA-C22.2 No. 144.1 (2006), CAN/CSA-C22.2 No. 182.4-1990
CSA Standard: Yes
cULus: Yes
UL Listing No: ANSI/UL 1863, ANSI/UL 985, ULC-S545, ANSI/UL 1023
UL Standard: Yes

UN SPSC: 43223306

CONSTRUCTION INFORMATION

Installation Location: In-Wall

DIMENSIONS

Depth (Metric): 9.4 cm

Depth (US): 3.7"

Height (Metric): 106.9 cm

Height (US): 42.1"

Width (Metric): 36.3 cm

Width (US): 14.3 in

Thickness (US): 20 Gauge

TECHNICAL INFORMATION

Humidity: 90% Relative Humidity (Non-Condensing)

Material: CRS

Mounting: Surface or Flush

Operating Temperature (Celsius): 0°C to 50°C