



UNIVERSAL 3 COMPONENT VIDEO CABLE (3 FT)

AC2303-BK | [On-Q](#)

FEATURES & BENEFITS

Improve the performance of your progressive scan video sources with the Universal 3 Component Video Cable. The oxygen-free copper center conductor and foam PE dielectric maintain a 75 Ohm characteristic impedance, and offer efficient signal transmission to deliver exceptional video detail, color and brightness. Available in 3 feet, 6 feet, 12 feet and 25 feet.

- In-Wall Rated for professional installations
- Constructed from 75Ohm oxygen-free copper
- Foil and braided shield to protect from interference
- Alternate color bands provided for universal A/V support

SPECIFICATIONS

GENERAL INFO

Color: Black

Connection Type: RCA

Special Features: In-wall rated for professional installations, Constructed from 75 ohm oxygen-free copper, Foil and braided shield to protect from interference, Alternate color bands provided for universal A/V support

LISTING AGENCIES/THIRD PARTY CERTIFICATIONS

UN SPSC: 26121616

DIMENSIONS

Depth (US): 0.82 in.

Height (US): 9.64 in.

Length (US): 3 ft.

Width (US): 7.87 in.

Weight: 0.21 lbs.

Height: 9.64 in.

TECHNICAL INFORMATION

Operating Temperature (Celsius): 75° C