
3.5MM TO L/R RCA AUDIO CABLE (25 FT)

AC2725-BK | [On-Q](#)



FEATURES & BENEFITS

Designed to provide quality music transfer from your mobile device to a fixed audio device. The unique "Case-Connect" design accommodates secure connections without requiring the removal of your device's protective case. This cable features two 27 AWG oxygen-free copper conductors, a drain wire, an aluminum foil shield to prevent unwanted EMI/RFI interference, and fully molded, gold-plated connectors providing strain relief for a quality connection. Available in 6 feet, 12 feet and 25 feet.

- In-wall, CMG/CL3/FT4 Tri-Rated jacket
- 22 AWG conductor construction
- "Case Connect" design accommodates secure connections without removing the device's protective case
- Supports a stereo audio signal

SPECIFICATIONS

GENERAL INFO

Color: Black

Connection Type: 3.5mm Audio/RCA

Special Features: Designed to provide quality music transfer from your mobile device to a fixed audio device

LISTING AGENCIES/THIRD PARTY CERTIFICATIONS

UN SPSC: 26121616

DIMENSIONS

Depth (US): 1.9 in.

Height (US): 8 in.

Length (US): 25 ft.

Width (US): 7.5 in.

Weight: 0.68 lbs.

Height: 8 in.

TECHNICAL INFORMATION

Operating Temperature (Celsius): 75° C