

---

## 14 FOOT CAT 6 PATCH CABLE, BLUE

AC3614-BE-V1 | [On-Q](#)



---

### FEATURES & BENEFITS

This component rated Cat 6 patch cable is constructed with a low profile, snagless boot that protects the tab from catching on other cables in a high density patch panel application. These patch cables are 100% tested and exceed the patch cable standards under TIA/EIA-568.

- 250MHz patch cable fully supports 10 Gigabit Ethernet speeds.
- UL verified to support the Cat 6 performance patch cable specification.
- Snagless overmold prevents insertion tab from catching on other cables.
- Patch cable exceeds 750 insertion cycles as specified in FCC part 68 Subpart F.

---

### SPECIFICATIONS

#### GENERAL INFO

Color: Blue

Pair Count: 4

Termination: 8P8C, contact area plated 50 microinches hard gold over 100 microinches of nickel

Type: Cat 6 Patch Cable

Input Plug Type: RJ45 Male

#### LISTING AGENCIES/THIRD PARTY CERTIFICATIONS

CSA Standard: Yes

UL Standard: Yes

UN SPSC: 43223303

#### DIMENSIONS

Diameter (Metric): 6.4 mm

Diameter (US): 0.25 in

#### CORD INFORMATION

Cord Length Metric: 4.3 m

Cord Length US: 14'

#### TECHNICAL INFORMATION

Material: Fire retardant PVC compound

Supported Standards: Verified to TIA/EIA-568-B.2-1 ISO/IEC 11801

Wire Gauge: 24 AWG