
48VDC, 100W POWER SUPPLY

PW1248 | [On-Q](#)



FEATURES & BENEFITS

DISCONTINUED- See PW1458

- Package includes a DC power supply with a 5.6 ft barrel connector plug and 1.5 ft AC power plug
- IEC C13/C14 connections
- Stacks neatly in enclosure with AC1031 power strip

SPECIFICATIONS

GENERAL INFO

Connection Type: DC Barrel

Type: Power Supply

ASSEMBLY/INSTALLATION INFORMATION

Mounting Hardware Included: Bracket, Velcro straps

LISTING AGENCIES/THIRD PARTY CERTIFICATIONS

UN SPSC: 39121006

DIMENSIONS

Depth (Metric): 6.8 cm

Depth (US): 2.67"

Height (Metric): 25.4 cm

Height (US): 10"

Width (Metric): 14.29 cm

Width (US): 5.625 in

CORD INFORMATION

Cord Length Metric: 45.7 cm AC in, 4x 6.1 cm DC out

Cord Length US: 18" AC", 4x 24.02" DC out

TECHNICAL INFORMATION

AC Voltage Input: 100-240VAC

Amps: 2.08

Efficiency: 0.78

Humidity: Operating Humidity: 10% to 90%; Storage: 5% to 90%

Mounting: Enclosure

Operating Temperature (Celsius): 0°C to 40°C

Storage Temperature: -4°F to 185°F

Volts (DC): 48

Watts: 100

Number Of Receptacles: 4