
USB A/B KEYSTONE ADAPTER INSERT

WP1221-BK | [On-Q](#)

FEATURES & BENEFITS

This USB 2.0 keystone adapter insert allows the customization of patch panels or wall plates to fit a specific installation, while providing a finished look. Including connection for a USB Type A in the front and USB Type B in the rear, it is also backwards compatible to USB v1.1 and will support data transfer rates of up to 480 Mbps.



- Includes USB 2.0 Type A front and Type B rear jacks
- Transfer Rates up to 480 Mbps
- Feed-through design
- Perfect for keystone patch panel application

SPECIFICATIONS

GENERAL INFO

Color: Black
Finish: smooth
Special Features: Phosphorus Bronze, (nut) Gold Flash Plated

LISTING AGENCIES/THIRD PARTY CERTIFICATIONS

RoHS: Yes
cULus: Yes
cUL Standard: Yes
UL Standard: Yes

DIMENSIONS

Height (US): 6"
Length (US): 0.65"
Width (US): 4"

TECHNICAL INFORMATION

Operating Temperature (Celsius): -10° C to 60° C

Storage Temperature: -40° C to 70° C

Supported Standards: UL, cULus, RoHS

Equipment Type: USB 2.0 A/B Coupler Keystone Insert