

---

## CATEGORY 5E RJ45 KEYSTONE CONNECTOR, IVORY

WP3450-IV | [On-Q](#)

---

### FEATURES & BENEFITS

The vertical design of this high quality insert makes punchdown termination easy. The insert is for use in all Keystone wall plates and is available in multiple colors, as well as convenient contractor packs.



**PRODUCT**  
ENVIRONMENTAL PROFILE

- High quality insert for use in multimedia wallplates
- Rear retention caps ensure secure wire termination
- Vertical design for easy punchdown termination
- T568A and T568B wiring labels included
- Meets Category 5e described in TIA/EIA-568-B.2
- Insertion and extraction life is 750 Cycles Min
- Jack housing is high-impact, flame resistant plastic, UL 94V-0
- Spring wire is phosphor bronze alloy plated with 50 micro-inch of gold over 100 micro-inches of nickel
- Also available in contractor pack of 50 (WP3450-WH-50)

---

### SPECIFICATIONS

#### GENERAL INFO

Color: Ivory  
Mod Jack Wiring: T568A or T568B  
Number Of Ports: 1  
Pair Count: 4  
Termination: IDC Wire Gauge: 22-24 AWG

#### LISTING AGENCIES/THIRD PARTY CERTIFICATIONS

RoHS: Yes  
cULus: Yes  
UL Listing No: ANSI/UL 1863; CAN/CSA-C22.2 No. 182.4-1990

## DIMENSIONS

Height (US): 0.87"

Length (Metric): 1.28"

Length (US): 1.28"

Width (US): 0.64"

Product Weight (US): 0.0255 lb

## TECHNICAL INFORMATION

Humidity: Max 93% non-condensing

Material: High Impact Plastic

Mounting: Keystone

Storage Temperature: Neg 40°F to 158°F