



CAT 5E KEYED RJ45 KEYSTONE CONNECTOR, BROWN

WP3458-BR | [On-Q](#)

FEATURES & BENEFITS

This high quality insert is for use in all Keystone Wall Plates



RoHS



PRODUCT
ENVIRONMENTAL PROFILE

Rear retention caps ensure secure wire termination.
T568A Cat 5e.
Vertical design for easy punchdown termination.

SPECIFICATIONS

GENERAL INFO

Cable Type: Cat5e
Color: Brown
Finish: 50 microinches 24K Hard Gold over 100 microinches Nickel
Pair Count: 4
Connection Type: 8P8C
Type: Keystone Insert
Input Plug Type: RJ45 Male

LISTING AGENCIES/THIRD PARTY CERTIFICATIONS

RoHS: Yes
CSA Listing Info: CAN/CSA-C22.2 No. 182.4-1990
CSA Standard: Yes
UL Listing No: ANSI/UL 1863
UL Standard: Yes
UN SPSC: 39121704

DIMENSIONS

Depth (Metric): 32.7 mm

Depth (US): 1.287"
Height (Metric): 22 mm
Height (US): .87"
Width (Metric): 16.2 mm
Width (US): .638 in

TECHNICAL INFORMATION

Current Max: 1.5 A
Humidity: Max Noncondensing 93%
Material: Phosphor Bronze Alloy
Mounting: Wallplate or Strap
OhmValue: 20 milliohm max contact resistance
Operating Temperature (Celsius): -10°C to 60°C
Storage Temperature: -40°C to 70°C
Receptacle Type: RJ45 Female
Number Of Receptacles: 1