



## CAT 5E KEYED RJ45 KEYSTONE CONNECTOR, LIGHT ALMOND

WP3458-LA | [On-Q](#)

### FEATURES & BENEFITS

This high quality insert is for use in all Keystone Wall Plates



**PRODUCT**  
ENVIRONMENTAL PROFILE

Rear retention caps ensure secure wire termination.  
T568A Cat 5e.  
Vertical design for easy punchdown termination.

### SPECIFICATIONS

#### GENERAL INFO

Cable Type: Cat5e  
Color: Light Almond  
Finish: 50 microinches 24K Hard Gold over 100 microinches Nickel  
Pair Count: 4  
Termination: via Punchdown Tool  
Connection Type: 8P8C  
Type: Keystone Insert  
Input Plug Type: RJ45 Male

#### LISTING AGENCIES/THIRD PARTY CERTIFICATIONS

RoHS: Yes  
CSA Listing Info: CAN/CSA-C22.2 No. 182.4-1990  
CSA Standard: Yes  
UL Listing No: ANSI/UL 1863  
UL Standard: Yes  
UN SPSC: 39121704

#### DIMENSIONS

Depth (Metric): 32.7 mm  
Depth (US): 1.287"  
Height (Metric): 22 mm  
Height (US): .87"  
Width (Metric): 16.2 mm  
Width (US): .638 in

#### TECHNICAL INFORMATION

Current Max: 1.5 A  
Humidity: Max Noncondensing 93%  
Material: Phosphor Bronze Alloy  
Mounting: Wallplate or Strap  
OhmValue: 20 milliohm max contact resistance  
Operating Temperature (Celsius): -10°C to 60°C  
Storage Temperature: -40°C to 70°C  
Receptacle Type: RJ45 Female  
Number Of Receptacles: 1