



## CAT 6A QUICK CONNECT RJ45 KEYSTONE INSERT, LIGHT ALMOND

WP346A-LA | [On-Q](#)

### FEATURES & BENEFITS



- Available in Blue, Black, Brown, White, Green, Gray, Ivory, Orange, Red, Yellow
- Easily terminate all four pairs using the Legrand Punch & Go Tool (AC3400)

### SPECIFICATIONS

#### GENERAL INFO

Cable Type: Cat 6a  
Color: Light Almond  
Termination: 8P8C, Phosphor Bronze alloy plated with 50 microinches of Gold  
Type: Keystone Insert  
Input Plug Type: RJ45

#### LISTING AGENCIES/THIRD PARTY CERTIFICATIONS

RoHS: Yes  
ETL Listed: Yes  
UN SPSC: 39121704

#### DIMENSIONS

Depth (Metric): 30.8 mm  
Depth (US): 1.21"  
Height (Metric): 19.3 mm  
Height (US): .76"  
Width (Metric): 16.9 mm  
Width (US): .665 in

#### CORD INFORMATION

Connector Type End One: RJ45 Female  
Connector Type End Two: Punchdown

#### **TECHNICAL INFORMATION**

Mounting: Wallplate or Strap  
Wire Gauge: 22 - 24 AWG  
Receptacle Type: RJ45 Female  
Number Of Receptacles: 1