
10X8 COMBO MODULE IDC WITH RJ31X

CO1110 | [On-Q](#)

FEATURES & BENEFITS

The 10x8 combo distributes up to 4 incoming telephone lines (110 IDC Punchdown) to 10 locations, and 1 GHz video to eight locations. The innovative mounting bracket includes a detachable platform for the coax splitter, allowing easy access to all termination ports during installation. The platform attaches securely to create a compact form factor that takes up minimal space in the enclosure.



- Eight way, 1 GHz passive digital HDTV cable splitter
- Coaxial splitter is compatible with existing and future networks such as VoIP and DOCSIS 3.0
- 10 way, 4-line 110 IDC Punchdown telecom module
- Includes RJ31X line seizure port for security installations
- Mounting infrastructure included
- UL listed

SPECIFICATIONS

GENERAL INFO

Cable Type: Cat 5, Cat 5e, Cat 6, Coaxial

Color: Black

Connection Type: F Connector, RJ31X

Type: Telecom/Video Module

Surge Protected: Splitter: Surge Withstand 6 kV Ring Wave Surge per IEEE C62.41 Category A3

LISTING AGENCIES/THIRD PARTY CERTIFICATIONS

UL Standard: Yes

UN SPSC: 43222819

DIMENSIONS

Height (Metric): 12.7 cm

Height (US): 5"
Length (Metric): 7.9 cm
Length (US): 3.1"
Width (Metric): 15.2 cm
Width (US): 6 in
Product Weight (US): 1.53 pounds

TECHNICAL INFORMATION

Material: 18 Gauge Cold Rolled Steel
Mounting: Enclosure
OhmValue: Splitter: Nominal impedance 75 Ohms
Operating Temperature (Celsius): -40°C to 60°C
Receptacle Type: IDC(10), F Connector(8), RJ31X(1)
Number Of Receptacles: 19