
10-WAY IDC TELEPHONE MODULE WITH RJ31X

TM1110 | [On-Q](#)



FEATURES & BENEFITS

This telephone module distributes up to 4 incoming telephone lines (110 IDC Punchdown) to 10 locations.



- Supports up to 10 locations
- Includes RJ31X line seizure port for security installations
- Mounting bracket included
- UL listed

SPECIFICATIONS

GENERAL INFO

Color: Black
Connection Type: Phosphor Bronze contacts, plated Gold over Nickel
Type: Telecom Module
Input Plug Type: RJ45 Male

LISTING AGENCIES/THIRD PARTY CERTIFICATIONS

cULus: Yes
UL Standard: Yes
UN SPSC: 43222819

DIMENSIONS

Height (Metric): 7.9 cm
Height (US): 3.1"
Length (Metric): 4.1 cm
Length (US): 1.6"
Width (Metric): 14.7 cm
Width (US): 5.78 in
Product Weight (US): 1.05 pounds

TECHNICAL INFORMATION

Connection Method: RJ45, RJ31X

Material: 18 Gauge Cold Rolled Steel

Mounting: Enclosure

Receptacle Type: 1x RJ31x, 11x 110 IDC Telecom

Number Of Receptacles: 12