



## KEYSTONE RECESSED F-CONN 75 OHM FOG WHITE

OR-KSFCNR | [Ortronics](#)

### FEATURES & BENEFITS

Ortronics F-connectors are often used with RG-6 and RG-59 75 ohm coaxial cable to connect equipment supporting cable TV(CATV), satellite TV, close circuit TV(CCTV), and security cameras.



- Recessed design:** Provides a more flush aesthetic look.
- Low profile connector:** Allows furniture to be placed closer to the wall.
- Designed for multiple coax cable styles:** Accepts both push-style and screw-style.
- 75 Ohm F-connector:** Ideal for cable/satellite TV, cable modems, and security cameras.
- TechChoice keystone footprint:** Fits in all TechChoice faceplates and housings.
- Rear loading module:** Allows for termination before and during the construction process.
- Integrates with Legrand | Wiremold :** Can be used in raceway, floor boxes, Poke-Thru, and work surface portals.

### SPECIFICATIONS

#### GENERAL INFO

Footprint: Keystone  
Number Of Ports: 1  
Termination: Female to Female Coupler  
Typical Applications: Cable TV(CATV), closed circuit TV (CCTV), satellite TV, security cameras, cable modems  
Product Series: Keystone  
Type: Video

#### LISTING AGENCIES/THIRD PARTY CERTIFICATIONS

RoHS: Yes  
CUL Listing No: E131600  
UL Listing No: E131600

#### CONSTRUCTION INFORMATION

Component 1: Plastic TechChoice Keystone Housing

Material 1: High Impact Thermoplastic ABS 94V-0

## **DIMENSIONS**

Depth (Metric): 22.23 mm

Depth (US): 0.875"

## **TECHNICAL INFORMATION**

Connection Method: Accepts push-on or screw-on style coax cables

OhmValue: 75 Ohm

Performance Rating: 3GHz

Equipment Type: F-connector