



TRACJACK MODULE F CONNECTOR F/F, ELECTRICAL IVORY

OR-63700006-13 | [Ortronics](#)

FEATURES & BENEFITS

TracJack Module provides a single F-connector coupler F/F with under .2dB of insertion loss at 2GHz (1/3 the loss of standard models). TracJack is a versatile single jack solution in a front-load footprint which allows a choice of up to six jacks/connectors to fit in a single gang plate



- F Connector coupler F/F
- Front removable
- Standard TracJack footprint

SPECIFICATIONS

GENERAL INFO

Color: Electrical Ivory
Footprint: TracJack
Number Of Ports: 2
Product Series: TracJack
Type: Video

LISTING AGENCIES/THIRD PARTY CERTIFICATIONS

RoHS: Yes
CUL Listing No: E131600
UL Listing No: E131600

CONSTRUCTION INFORMATION

Component 1: Plastic Series II Housing
Component 2: F-Connector female/female coupler
Material 1: High Impact Thermoplastic ABS 94V-0

Material 2: Feed-through, RG6/59 (G-F81TN)

DIMENSIONS

Depth (Metric): 14.48 mm

Height (Metric): 23.37 mm

Height (US): 0.92"

Width (Metric): 18.54 mm

TECHNICAL INFORMATION

Equipment Type: F Conn Coax

BUY AMERICAN ACT COMPLIANCE

Country Of Origin: MALAYSIA

Buy American Act Status: Exception

Note: Contact Customer Support for Buy American Act options