



TRACJACK RECESSED F-CONN 75 OHM BLACK

OR-63700087-00 | [Ortronics](#)

FEATURES & BENEFITS

Ortronics F-connectors are often used with RG-6 and RG-59 75 ohm coaxial cable to connect equipment supporting cable TV(CATV), satellite TV, close circuit TV(CCTV), and security cameras.



- Recessed design:** Provides a more flush aesthetic look.
- Low profile connector:** Allows furniture to be placed closer to the wall.
- Designed for multiple coax cable styles:** Accepts both push-style and screw-style.
- 75 Ohm F-connector:** Ideal for cable/satellite TV, cable modems, and security cameras.
- Standard TracJack footprint:** Fits in all TracJack faceplates and housings.
- Front removable module:** Less intrusive access for adds, moves, changes.
- Integrates with Legrand | Wiremold :** Can be used in raceway, floor boxes, Poke-Thru, and work surface portals.

SPECIFICATIONS

GENERAL INFO

Footprint: TracJack
Number Of Ports: 1
Termination: Female to Female Coupler
Typical Applications: Cable TV(CATV), closed circuit TV (CCTV), satellite TV, security cameras, cable modems
Product Series: TracJack
Type: Video

LISTING AGENCIES/THIRD PARTY CERTIFICATIONS

RoHS: Yes
CUL Listing No: E131600
UL Listing No: E131600

CONSTRUCTION INFORMATION

Component 1: Plastic TracJack Housing

Material 1: High Impact Thermoplastic ABS 94V-0

DIMENSIONS

Depth (Metric): 22.23 mm

Depth (US): 0.875"

TECHNICAL INFORMATION

Connection Method: Accepts push-on or screw-on style coax cables

OhmValue: 75 Ohm

Performance Rating: 3GHz

Equipment Type: F-connector