

---

## 25-PAIR VOICE GRADE CABLE ASSEMBLY, M/BLUNT, 25'

OR-804025PX025-1BE | [Ortronics](#)



---

### FEATURES & BENEFITS

25-Pair Voice Grade Cable Assembly, M/Blunt, 25'



- Factory terminated voice grade cables
- Supported by a family of lengths and terminations
- 24 AWG solid copper construction

---

### SPECIFICATIONS

#### GENERAL INFO

Cable Type: 25-Pair UTP Non Plenum  
Color Cable Jacket: Beige  
Termination: 50-Pin (RJ21) M/Blunt  
Typical Applications: Voice equipment, connectorized blocks

#### LISTING AGENCIES/THIRD PARTY CERTIFICATIONS

RoHS: Yes  
CSA Listing Info: LR 90894  
CUL Listing No: E131601  
UL Listing No: E131600

#### CONSTRUCTION INFORMATION

Component 1: 25-Pair, 24 AWG, voice grade cable  
Component 2: 50-Pin male telco connector (RJ21)  
Finish Plating 2: 30 Micro inches of gold over nickel plating in mating contact area  
Material 1: 24 AWG, solid copper conductors, PVC insulation, twisted pairs, PVC jacket  
Material 2: High strength copper alloy contacts| High impact Thermo Plastic housings and covers

## **DIMENSIONS**

Diameter (Metric): 8.7 mm

Diameter (US): 0.34"

Length (Metric): 7.62 m

## **CORD INFORMATION**

Connector Type End One: 50-Pin telco connector - male

Connector Type End Two: Blunt cable end

Jacket Rating: CMR/PVC

Cord Length US: 25'

Pinning: Pin 1 to 1 standard 25-pair color code

## **TECHNICAL INFORMATION**

Category Rating: Cat1

OhmValue: 100 Ohm

Performance Rating: Voice

Sort Termination: 6

Wire Gauge: 24 AWG