



## CLARITY 6 MODULAR PATCH CORD, 7', BLUE

OR-MC607-06 | [Ortronics](#)

### FEATURES & BENEFITS

Clarity 6 Modular Patch Cord, blue, 7', Category 6, four-pair UTP stranded 24 AWG PVC/CM, center tuned with Clarity 6 connecting hardware for optimum Category 6 installed performance using Ortronics Paralign 2 pair-positioning technology



**PRODUCT**  
ENVIRONMENTAL PROFILE

- **ETL third party tested and verified to TIA/EIA 568B.2-1 Category 6 component specifications:** Ensures Category 6 component performance.
- **Each cord is factory tested:** Ensures every cord shipped meets Category 6 component specifications.
- **Center tuned technology:** Elevates the performance of Clarity 6 connector union.
- **Paralign 2 pair-positioning technology:** Maintains pair integrity through the plug termination allowing mating hardware to be designed/tuned to these cords.
- **Snagless plug design:** Protects plugs when pulling through pathways or cable managers.
- **Premium conductor cordage:** Reliable performance and durable cord life.
- **Compatible with both T568A and T568B wiring:** Provides universal wiring ability.
- **Improved signal to noise ratio:** More transparent signal path is field measurable in a link or channel.
- **Backwards compatible to Category 3, 5, and 5e:** Supports lower category installations and components.

### SPECIFICATIONS

#### GENERAL INFO

Cable Type: Four-pair stranded UTP non-plenum

Color Cable Jacket: Blue

Performance Category: Cat 6 component compliant

Termination: 8-Pos Mod

Typical Applications: IEEE 802.3 1000Base-T (Gigabit Ethernet), TIA/EIA-854 1000Base-TX, ATM CB1G

Product Series: Clarity

Type: Patch Cords and Cables

#### LISTING AGENCIES/THIRD PARTY CERTIFICATIONS

RoHS: Yes

ETL Listing No: 3013270-006

ETL Listed: Yes

FCC Standard: Yes

## CONSTRUCTION INFORMATION

Component 1: Cable

Component 2: Eight-position plug assembly

Component 3: Modular plug IDC contacts

Component 4: Paralign 2 pair segregation and strain relief

Finish Plating 3: 50 Micro inch elective gold plating over nickel

Material 1: 24 AWG bare copper stranded conductors, PVC insulation, PVC jacket

Material 2: Polycarbonate plug housing and conductor positioning sled

Material 3: Phosphor-bronze contacts

Material 4: Molded Polypropylene Copolymer

## DIMENSIONS

Diameter (Metric): 7.5 mm

Diameter (US): 0.29"

Length (Metric): 2.13 m

## CORD INFORMATION

Connector Type End One: Plug, HSG, eight-contact, RJ45, high performance

Connector Type End Two: Plug, HSG, eight-contact, RJ45, high performance

Jacket Rating: CM

Cord Length US: 7'

Min Bend Radius: 1.00"

Pinning: Straight 1-1, 2-2, 3-3, etc.

## TECHNICAL INFORMATION

Category Rating: Cat 6 component compliant

OhmValue: 100 Ohm

Performance Rating: Cat6

Sort Termination: 3

Wire Gauge: 24 AWG

## BUY AMERICAN ACT COMPLIANCE

Country Of Origin: MEXICO

Buy American Act Status: Trade Agreement Act Compliant

