

---

REPLACED BY PHD5E6U24HM. PLEASE  
ACCESS PRODUCT INFORMATION FOR  
PHD5E6U24HM



OR-851044971 | [Ortronics](#)

---

## FEATURES & BENEFITS

Replaced by PHD5E6U24HM. Please access product information for PHD5E6U24HM.



- **High density design** Maximizes use of rack space.
- **110 termination:** Easy and reliable termination.
- **Wire management bar included:** Ensures proper bend radius and strain relief.
- **Front and rear designation strips:** Makes identification and designation easy.

---

## SPECIFICATIONS

### GENERAL INFO

Mod Jack Wiring: T568B  
Number Of Ports: 24  
Product Series: Clarity  
Type: Patch Panels

### ASSEMBLY/INSTALLATION INFORMATION

Installation Tips: The cables should be routed from both sides of the Relay Rack rather than from one side only. Maintain pair twist to within .50" (13 mm) of point of termination for maximum data performance.

### LISTING AGENCIES/THIRD PARTY CERTIFICATIONS

RoHS: Yes  
CSA Listing Info: LR 90894  
CUL Listing No: E131600  
UL Listing No: E131600

### CONSTRUCTION INFORMATION

Component 1: Panel  
Component 2: Eight-port jack housing  
Component 3: Linear modular contact  
Component 4: 110D connecting block housing  
Component 5: IDC contact  
Finish Plating 1: Painted black - texture with white silkscreen  
Finish Plating 3: 50 micro inch gold or GTX  
Finish Plating 5: 63/37 Tin Lead Plating  
Material 1: 0.125" Aluminum  
Material 2: ABS UL94V-0  
Material 3: Phosphor Bronze  
Material 4: ABS UL94V-0  
Material 5: Phosphor Bronze

## **DIMENSIONS**

Cable Diameter Range: 22-26 AWG  
Depth (Metric): 3.175 mm  
Height (Metric): 88.9 mm  
Height (US): 3.5"  
Width (Metric): 482.6 mm

## **TECHNICAL INFORMATION**

Category Rating: Cat5e  
Performance Rating: Cat5e  
Product Fits Into: Mighty Mo Racks and Cabinets