
REAR LOAD ANGLED HIGH DENSITY JACK PANEL KIT FOR 24 CLARITY 6 OR 5E PANEL JACKS.

OR-PHAPJU24 | [Ortronics](#)

FEATURES & BENEFITS

Rear load angled high density jack panel kit for 24 Clarity 6 or 5E panel jacks. It occupies 1 rack unit and measures 19" x 1.75".



PRODUCT
ENVIRONMENTAL PROFILE

- **Jacks rear load into panels:** All terminations done from rear of panel.
- **New positive jack latching design:** Secure mounting of jacks into panel.
- **Recessed design with lower mounted profile:** Directs cords more easily to vertical management.
- **High density solution:** Maximizes rack space.
- **Panel jacks support snap-in icons:** Easy designation of ports.
- **Universal wiring labels on panel jacks:** Supports both T568B and T568A wiring schemes.
- **Silkscreened 1-48:** Easy port identification.

SPECIFICATIONS

GENERAL INFO

Color: Black with blue silkscreen
Footprint: Clarity 6 or 5E rear load PJ series panel jacks
Mod Jack Wiring: Field defined
Number Of Ports: Up to 24
Product Series: Clarity
Type: Patch Panels

ASSEMBLY/INSTALLATION INFORMATION

Installation Tips: Terminate panel jack and then rear load into the panel, maintaining minimum bend radius of four times the cable diameter.
Mounting Hardware Included: Yes

LISTING AGENCIES/THIRD PARTY CERTIFICATIONS

RoHS: Yes
CUL Listing No: E131600
UL Listing No: E131600
UL Standard: Yes

CONSTRUCTION INFORMATION

Component 1: Panel
Component 2: Patch Panel Mounting Screws #12-24 x 5/8"
Finish Plating 1: Black with blue silkscreen
Finish Plating 2: Black
Material 1: .090 aluminum
Material 2: Steel

DIMENSIONS

Depth (Metric): 38.86 mm
Height (Metric): 44.45 mm
Height (US): 1.75"
Width (Metric): 482.6 mm

TECHNICAL INFORMATION

Category Rating: Cat6a
Performance Rating: Cat6a

BUY AMERICAN ACT COMPLIANCE

Country Of Origin: UNITED STATES OF AMERICA
Buy American Act Status: Buy American Act Compliant

