
REAR LOAD ANGLED HIGH DENSITY JACK PANEL KIT FOR 72 CLARITY 6 OR 5E PANEL JACKS

OR-PHAPJU72 | [Ortronics](#)



FEATURES & BENEFITS

Rear load angled high density jack panel kit for 72 Clarity 6 or 5E panel jacks



PRODUCT
ENVIRONMENTAL PROFILE

- Jacks rear load into panels
- New positive jack latching design
- Recessed design with lower mounted profile
- High density panel jack solution
- Panel jacks support snap-in icons
- Universal wiring labels on panel jacks
- Silkscreened 1-72

SPECIFICATIONS

GENERAL INFO

Color: Black with blue silkscreen
Footprint: Clarity 6 or 5E rear load PJ series panel jacks
Mod Jack Wiring: Field defined
Number Of Ports: Up to 72
Product Series: Clarity
Type: Patch Panels

ASSEMBLY/INSTALLATION INFORMATION

Installation Tips: Terminate panel jack and then rear load into the panel, maintaining minimum bend radius of four times the cable diameter.

Mounting Hardware Included: Yes

LISTING AGENCIES/THIRD PARTY CERTIFICATIONS

RoHS: Yes

CUL Listing No: E131600
UL Listing No: E131600
UL Standard: Yes

CONSTRUCTION INFORMATION

Component 1: Panel
Component 2: Patch Panel Mounting Screws #12-24 x 5/8"
Finish Plating 1: Black with blue silkscreen
Finish Plating 2: Black
Material 1: .090 aluminum
Material 2: Steel

DIMENSIONS

Depth (Metric): 38.86 mm
Height (Metric): 88.90 mm
Height (US): 3.5"
Width (Metric): 482.6 mm

TECHNICAL INFORMATION

Category Rating: Cat6a
Performance Rating: Cat6a

BUY AMERICAN ACT COMPLIANCE

Country Of Origin: UNITED STATES OF AMERICA
Buy American Act Status: Buy American Act Compliant

