



## SERIES II, TWO-PORT, USOC (RJ61X), 180 DEGREE

OR-60900038 | [Ortronics](#)

### FEATURES & BENEFITS

Series II Module provides two RJ61X, eight-position USOC wired jacks in a one unit footprint. Series II is a family of front removable snap-in modules that make moves, adds and changes easy and time saving. The rugged high strength construction of Series II makes it one of Ortronics most popular workstation choices



- Linear 110 paired punch down
- Front removable
- Rugged snap-in design
- Icon compatible

### SPECIFICATIONS

#### GENERAL INFO

Color: Fog White  
Footprint: Series II  
Number Of Ports: 2  
Product Series: Clarity  
Type: Jacks and Modules

#### LISTING AGENCIES/THIRD PARTY CERTIFICATIONS

RoHS: Yes  
CUL Listing No: E131600  
UL Listing No: E131600

#### CONSTRUCTION INFORMATION

Component 1: Plastic Series II Housing  
Component 2: Two arrays of eight linear modular contacts

Component 3: IDC contacts, 110 D4

Component 4: Printed circuit board

Finish Plating 2: Nickel plating and a minimum of 50 micro inches of selective gold plating in contact area

Finish Plating 3: Nickel plating and tin lead over plate

Material 1: High Impact Thermoplastic ABS 94V-0

Material 2: Phosphor bronze

Material 3: Phosphor bronze

Material 4: Two-sided FR-4 epoxy resin/glass base with solder mask

#### **DIMENSIONS**

Depth (Metric): 32.77 mm

Height (Metric): 23.37 mm

Height (US): 0.92"

Width (Metric): 48.26 mm

#### **TECHNICAL INFORMATION**

Performance Rating: USOC eight-position