



SERIES II, ONE-PORT CATEGORY 5E, T568B, 180 DEGREE, WIREMOLD IVORY

OR-60950008-99 | [Ortronics](#)

FEATURES & BENEFITS

[DISCONTINUED]

25-Pair Voice Grade Cable Assembly, M/Blunt, 10'



- **TIA/EIA Category 5e performance:** Ensures installed link and channel performance.
- **Linear 110 paired punch down:** Faster than other termination methods.
- **Front removable:** Less intrusive access for adds, moves, changes.
- **Rugged snap-in design:** Quick and easy.
- **Icon compatible:** Supports TIA/EIA 606 standard.

SPECIFICATIONS

GENERAL INFO

Discontinued: Yes
Color: Wiremold Ivory
Footprint: Series II
Number Of Ports: 1
Product Series: Clarity
Type: Jacks and Modules

LISTING AGENCIES/THIRD PARTY CERTIFICATIONS

RoHS: Yes
CUL Listing No: E131600
UL Listing No: E131600

CONSTRUCTION INFORMATION

Component 1: Plastic Series II Housing

Component 2: Array of eight linear modular contacts

Component 3: IDC contacts, 110 D4

Component 4: Printed circuit board

Finish Plating 2: Nickel plating and a minimum of 50 micro inches of selective gold plating in contact area

Finish Plating 3: Nickel plating and tin lead over plate

Material 1: High Impact Thermoplastic ABS 94V-0

Material 2: Phosphor bronze

Material 3: Phosphor bronze

Material 4: Two-sided FR-4 epoxy resin/glass base with solder mask

DIMENSIONS

Depth (Metric): 32.77 mm

Height (Metric): 23.37 mm

Height (US): 0.92"

Width (Metric): 48.26 mm

TECHNICAL INFORMATION

Category Rating: Cat 5e

Wire Gauge: 22-26 AWG