



TRACJACK CATEGORY 5E, T568A/B, 180 DEGREE, BLACK

OR-63750001-00 | [Ortronics](#)

FEATURES & BENEFITS

Category 5e TracJack Module supports T568A or B wiring with 110 IDC termination. TracJack is a versatile single jack solution in a front-load footprint which allows a choice of up to six jacks/connectors to fit in a single gang plate



- **Meets TIA/EIA Category 5e:** Ensures installed Category 5e link and channel performance.
- **Front removable:** Less intrusive access for adds, moves, changes.
- **Traditional 110 termination:** Standard termination practices.
- **Standard TracJack footprint:** Fits in all TracJack faceplates and housings.
- **Icon compatible, with Category 5e marking on jack face:** Supports 606 designation requirements.

SPECIFICATIONS

GENERAL INFO

Color: Black
Footprint: TracJack
Number Of Ports: 1
Product Series: Clarity
Type: Jacks and Modules

LISTING AGENCIES/THIRD PARTY CERTIFICATIONS

RoHS: Yes
CUL Listing No: E131600
UL Listing No: E131600

CONSTRUCTION INFORMATION

Component 1: Plastic Series II Housing
Component 2: Eight linear modular contacts
Component 3: IDC contacts, 110 D2

Component 4: Printed circuit board

Finish Plating 2: Nickel plating and a minimum of 50 micro inches of selective gold plating in contact area

Finish Plating 3: Nickel plating and tin lead over plate

Material 1: High Impact Thermoplastic ABS 94V-0

Material 2: Phosphor bronze

Material 3: Phosphor bronze

Material 4: Two-sided FR-4 epoxy resin/glass base with solder mask

DIMENSIONS

Depth (Metric): 34.04 mm

Height (Metric): 23.37 mm

Height (US): 0.92"

Width (Metric): 18.54 mm

TECHNICAL INFORMATION

Category Rating: Cat 5e

Wire Gauge: 22-26 AWG