



TRACJACK FACEPLATE, STAINLESS, TWO-PORT (SINGLE GANG)

OR-40300454 | [Ortronics](#)

FEATURES & BENEFITS

Ortronics Single Gang Stainless Steel Faceplate accepts front-loading TracJack modules and includes two snap-in label fields



- Stainless steel construction
- Smooth low profile design
- Recessed label fields
- Easily accepts snap-in TracJacks
- Front load module approach

SPECIFICATIONS

GENERAL INFO

Color: Stainless steel
Footprint: TracJack
Number Of Ports: 2
Product Series: Clarity
Type: Plates and Boxes

ASSEMBLY/INSTALLATION INFORMATION

Mounting Hardware Included: #6-32 Oval Slot Screw 304 Stainless Steel (2 ea)

LISTING AGENCIES/THIRD PARTY CERTIFICATIONS

RoHS: Yes
CUL Listing No: E131600
UL Listing No: E131600
UL Standard: Yes

CONSTRUCTION INFORMATION

Component 1: Stainless Steel TracJack Faceplate

Material 1: Brushed Stainless Steel

DIMENSIONS

Depth (Metric): 3.81 mm

Height (Metric): 114.3 mm

Height (US): 4.5"

Width (Metric): 69.85 mm