
HDJ 2 HOLE FACEPLATE, FOG WHITE

OR-403HDJ12 | [Ortronics](#)



FEATURES & BENEFITS

Ortronics Single Gang Plastic Faceplate accepts rear loading high density jack (HDJ) modules and includes two snap-in label fields.



- **Low profile design:** Blends with most environments.
- **Recessed label fields:** Supports TIA/EIA 606 standard.
- **Accepts snap-in High Density Jacks (HDJ):** Easily field configured.
- **Textured finish:** Hides scuffs.
- **Oval mounting holes:** Assists proper alignment.

SPECIFICATIONS

GENERAL INFO

Color: Fog White
Footprint: High Density Jack (HDJ)
Number Of Ports: 2
Product Series: High Density
Type: Plates and Boxes

ASSEMBLY/INSTALLATION INFORMATION

Mounting Hardware Included: #6-32*25 mm Screw, Binding Head (2 ea)

LISTING AGENCIES/THIRD PARTY CERTIFICATIONS

RoHS: 1
CUL Listing No: E131600
UL Listing No: E131600
UL Standard: Yes

CONSTRUCTION INFORMATION

Component 1: Plastic HDJ faceplate

Component 2: #6-32*25 mm Screw, Binding Head (2 ea)

Material 1: High Impact Thermoplastic PC Polycarbonate 94V-0

DIMENSIONS

Depth (Metric): 7.87 mm

Depth (US): 0.31"

Height (Metric): 114.30 mm

Height (US): 4.5"

Width (Metric): 65.6 mm

Width (US): 2.74"

TECHNICAL INFORMATION

Frequency: High Density

Watts: up to 2 HDJ modules

Capacity: up to 2 HDJ modules

BUY AMERICAN ACT COMPLIANCE

Country Of Origin: TAIWAN

Buy American Act Status: Trade Agreement Act Compliant