



TRACJACK PLASTIC SURFACE MOUNT BOX FOR TWO MODULES, ELECTRICAL IVORY

OR-40400054-13 | [Ortronics](#)

FEATURES & BENEFITS

[DISCONTINUED]

Clarity 5E Angled TracJack, ETL verified to TIA Category 5e component specification, is front-loading and front removable. New universal T568A/B wiring label and tapered wiring towers simplify termination. Center tuned to Clarity 5E patch cords for significant performance above Category 5e.



- Low profile compact design
- Base plate and snap-on cover design
- Front-load module approach
- Recessed label fields
- Textured finish
- Holds two TracJack modules

SPECIFICATIONS

GENERAL INFO

Discontinued: Yes
Color: Electrical Ivory
Footprint: TracJack
Number Of Ports: 2
Product Series: Clarity
Type: Plates and Boxes

ASSEMBLY/INSTALLATION INFORMATION

Mounting Hardware Included: #6-20*19 mm (Panhead) (2 ea)

LISTING AGENCIES/THIRD PARTY CERTIFICATIONS

RoHS: Yes
CUL Listing No: E131600
UL Listing No: E131600
UL Standard: Yes

CONSTRUCTION INFORMATION

Component 1: Plastic TracJack Surface Box
Material 1: High Impact Thermoplastic ABS 94V-0

DIMENSIONS

Depth (Metric): 29.46 mm
Height (Metric): 55.37 mm
Height (US): 2.18"
Width (Metric): 64.26 mm

TECHNICAL INFORMATION

Capacity: Up to two modules