



TRACJACK PLASTIC SURFACE MOUNT BOX FOR UP TO SIX MODULES

OR-40400056 | [Ortronics](#)

FEATURES & BENEFITS

Replaced By 404TJ6TracJack Plastic Surface Mount Box for up to six modules



- Low profile compact design
- Base plate and snap-on cover design
- Front-load module approach
- Recessed label fields
- Textured finish
- Holds four TracJack modules
- Built in fiber/cable storage ring

SPECIFICATIONS

GENERAL INFO

Color: Fog White
Footprint: TracJack
Number Of Ports: 6
Product Series: Clarity
Type: Plates and Boxes

ASSEMBLY/INSTALLATION INFORMATION

Mounting Hardware Included: #6-32*25 mm Screw, Binding Head (2 ea) | #6-20*19 mm (Panhead) (2 ea)

LISTING AGENCIES/THIRD PARTY CERTIFICATIONS

RoHS: Yes
CUL Listing No: E131600
UL Listing No: E131600
UL Standard: Yes

CONSTRUCTION INFORMATION

Component 1: Plastic TracJack Surface Box

Material 1: High Impact Thermoplastic ABS 94V-0

DIMENSIONS

Depth (Metric): 29.46 mm

Height (Metric): 91.44 mm

Height (US): 3.6"

Width (Metric): 176.78 mm

TECHNICAL INFORMATION

Capacity: Up to six modules