



## TRACJACK PLASTIC SURFACE MOUNT BOX FOR TWO MODULES, FOG WHITE

OR-404TJ2 | [Ortronics](#)

### FEATURES & BENEFITS

Ortronics TracJack Surface Mount Outlet Boxes accept front-loading TracJack modules and provide snap-on covers and snap-in label fields. Boxes are supplied with screws and double-sided adhesive tape for mounting onto almost any surface. Meet UL2043 and are suitable for installation in air handling spaces (ie plenum spaces)



- Low profile compact design
- Suitable for installation in air handling spaces
- Base plate and snap-on cover design
- Front-load module approach
- Textured finish
- Holds two TracJack modules
- Recessed label fields
- Compatible with LabelMO XL
- Designed to seamlessly intergrate with Wiremold 2700, 2800 and 2900 raceways

### SPECIFICATIONS

#### GENERAL INFO

Color: Fog White  
Footprint: TracJack  
Number Of Ports: 2  
Product Series: Clarity  
Type: Plates and Boxes

#### ASSEMBLY/INSTALLATION INFORMATION

Mounting Hardware Included: #6-20\*19 mm (Pan head) 2ea

#### LISTING AGENCIES/THIRD PARTY CERTIFICATIONS

RoHS: Yes

CUL Listing No: UL 1863 UL 2043

UL Listing No: E131600

UL Standard: UL 1863, UL 2043

#### **CONSTRUCTION INFORMATION**

Component 1: Plastic TracJack Surface Box

Material 1: High Impact Thermoplastic ABS 94V-0

#### **DIMENSIONS**

Depth (Metric): 30.48 mm

Depth (US): 1.20"

Height (Metric): 57.66 mm

Height (US): 2.27"

Width (Metric): 65.79 mm

Width (US): 2.59"

#### **TECHNICAL INFORMATION**

Capacity: Up to two TracJack modules

#### **BUY AMERICAN ACT COMPLIANCE**

Country Of Origin: TAIWAN

Buy American Act Status: Trade Agreement Act Compliant