

---

## CAT6A SHIELDED 48 PORT PANEL ANGLED, WITH INDIVIDUAL SHIELDED KEYSTONE JACKS

OR-PHATKS6A48 | [Ortronics](#)



---

### FEATURES & BENEFITS

48 port Cat6A shielded recessed angled panel with 48 rear loading TKS6A shielded jacks. Includes rear cable management, and grounding lug. Occupies 2 rack unit of space 3.5" x 19"



- **Meets Category 6A component standard:** Ensures standards compliance
- **Easy lace wiring** Reduces wiring time
- **Easy to follow universal wiring label:** Quick and user-friendly, eliminates confusion
- **Rear loading:** preferred mounting for panels
- **Supplied rear cable management :** supports good cabling practices.
- **RoHS compliant:** Lead free

---

### SPECIFICATIONS

#### GENERAL INFO

Category Performance Application: Category 6A shielded  
Color: Black & silver  
Footprint: Keystone  
Mod Jack Wiring: Universal T568A/B  
Number Of Ports: 48  
Termination: Insulation displacement contacts  
Type: Patch Panels

#### LISTING AGENCIES/THIRD PARTY CERTIFICATIONS

RoHS: Yes  
CUL Listing No: E131600  
FCC Standard: Yes  
UL Listing No: E131600

#### CONSTRUCTION INFORMATION

Component 1: Angled Patch Panel  
Component 2: Cast metal Cat6A jack  
Component 3: Rear cable management bar  
Material 1: .065 steel  
Material 2: Zinc alloy housing  
Material 3: round edge flat steel

#### **DIMENSIONS**

Depth (Metric): 180.6 mm  
Depth (US): 7.11 in  
Height (US): 3.47 in  
Width (Metric): 482.6 mm  
Width (US): 19.00"  
Rack Units: 2

#### **TECHNICAL INFORMATION**

Category Rating: Cat 6a component compliant  
Performance Rating: Cat6a