
CATEGORY 6A TECHCHOICE MODULAR PATCH CORD, 3', WHITE

SPCA6A03-09 | [Ortronics](#)



FEATURES & BENEFITS

TechChoice category 6A modular patch cords are available in your choice of 8 standard lengths and 4 stocked colors. Each 4-pair, 26 AWG stranded, PVC cord is factory tested to ensure component and channel performance.

- **Each cord is factory tested:** Ensures every cord will perform to Cat 6A specs.
- **Tuned quality cordage:** Reliable performance and durable cord life.
- **Compatible with both T568A and T568B wiring:** Provides universal wiring ability.
- **Controlled signal to noise ratio:** better signal path in a link or channel.
- **Backwards compatible to Category 6 & 5e:** Supports lower category installations and components.

SPECIFICATIONS

GENERAL INFO

Cable Type: Category 6A, UTP 4-pair, 26 AWG stranded, non plenum

Color: White

Color Cable Jacket: White

Performance Category: Category 6a

Termination: 8-Pos Mod

Product Series: TechChoice

Type: Patch Cords and Cables

LISTING AGENCIES/THIRD PARTY CERTIFICATIONS

RoHS: Yes

CONSTRUCTION INFORMATION

Component 1: 4-pair, 26 gauge stranded cord

Component 2: Eight-position plug assembly with IDC contacts

Material 1: 26 AWG tinned copper stranded conductors, HDPE insulation, PVC jacket

Material 2: Polycarbonate plug with gold plated Phosphor-bronze IDC contacts

DIMENSIONS

Diameter (Metric): 5.89 mm

Diameter (US): .232"

Length (Metric): .91m

CORD INFORMATION

Connector Type End One: Plug, eight-contact, RJ45, category 6a performance

Connector Type End Two: Plug, eight-contact, RJ45, category 6a performance

Cord Length US: 3'

Min Bend Radius: .93"

Pinning: Straight 1-1, 2-2, 3-3, etc.

TECHNICAL INFORMATION

Category Rating: Cat6a

OhmValue: 100

Performance Rating: Category 6A, 10G UTP

Wire Gauge: 26 AWG

BUY AMERICAN ACT COMPLIANCE

Country Of Origin: MEXICO

