



## KEYSTONE TECHCHOICE RECTANGULAR STYLISTICS FRAME, 4-PORT, FOG WHITE

OR-KSDS4 | [Ortronics](#)

### FEATURES & BENEFITS

Keystone Rectangular (GFCI) Type Plastic Duplex Frame accepts four rear-loading keystone modules. It is compatible with many cable delivery systems that can house rectangular electrical outlets.



- **Matches rectangular electrical outlet (GFI) footprint:** Supports use with electrical delivery system.
- **Field configurable with keystone jacks:** Design or site flexibility for new or retrofit.
- **Supports keystone jack footprint:** Broad offering of connector options.
- **Choice of colors:** Compatible with many environments.

### SPECIFICATIONS

#### GENERAL INFO

Color: Fog White  
Footprint: Keystone  
Number Of Ports: 4  
UL Standards Tested: UL 1863  
Product Series: TechChoice Keystone  
Type: Plates boxes frames

#### ASSEMBLY/INSTALLATION INFORMATION

Mounting Hardware Included: #6-32\*25 mm Combo Head, TP-2 (2 ea)

#### LISTING AGENCIES/THIRD PARTY CERTIFICATIONS

RoHS: Yes  
CUL Listing No: E131600  
UL Listing No: E131600  
UL Standard: Yes

## **CONSTRUCTION INFORMATION**

Component 1: Plastic Keystone Mounting Frame  
Component 2: #6-32\*25 mm Combo Head, TP-2 (2 ea)  
Material 1: High Impact Thermoplastic

## **DIMENSIONS**

Depth (Metric): 11.2 mm  
Depth (US): .44"  
Height (Metric): 106.7 mm  
Height (US): 4.20"  
Width (Metric): 37.1 mm  
Width (US): 1.46"

## **BUY AMERICAN ACT COMPLIANCE**

Country Of Origin: TAIWAN