



CATEGORY 6 KEYSTONE JACK, ELECTRICAL IVORY

OR-KS6-13 | [Ortronics](#)

FEATURES & BENEFITS

Category 6 Keystone jack, 8-position, 180 degree exit, icon compatible, T568A/B wiring, Electrical Ivory Package of 25. TechChoice keystone jacks and modules feature an easy-to-follow universal wiring label and support standard termination using a 110-impact tool. The keystone footprint allows for the greatest flexibility in installation scheduling because its rear insertion into the faceplate allows the technician to complete the termination before and during the construction process. Package of 25.



- **Category 6:** Standards compliant.
- **Easy to follow universal wiring label:** Quick and user-friendly, eliminates confusion.
- **Rear loading:** Preferred mounting for panels.
- **Icon compatible:** Supports 606 designation requirements.
- **RoHS compliant:** Lead free.

SPECIFICATIONS

GENERAL INFO

Color: Electrical Ivory
Footprint: Keystone
Number Of Ports: 1
Performance Category: Cat 6 component compliant
UL Standards Tested: UL 1863
Product Series: TechChoice
Type: Jacks and Modules

LISTING AGENCIES/THIRD PARTY CERTIFICATIONS

RoHS: Yes
CUL Listing No: E131600
UL Listing No: E131600

DIMENSIONS

Depth (Metric): 28.7mm
Depth (US): 1.13 in
Height (Metric): 22.3mm
Height (US): .88 in
Width (Metric): 16.25mm
Width (US): .64 in

TECHNICAL INFORMATION

Category Rating: Cat 6 component compliant
Performance Rating: Cat6

BUY AMERICAN ACT COMPLIANCE

Country Of Origin: CHINA
Buy American Act Status: Exception
Note: Contact Customer Support for Buy American Act options