

---

## CATEGORY 6 KEYSTONE JACK, GRAY

OR-KS6-78 | [Ortronics](#)

---

### FEATURES & BENEFITS

Category 6 Keystone jack, 8-position, 180 degree exit, icon compatible, T568A/B wiring, Gray Package of 25. TechChoice keystone jacks and modules feature an easy-to-follow universal wiring label and support standard termination using a 110-impact tool. The keystone footprint allows for the greatest flexibility in installation scheduling because its rear insertion into the faceplate allows the technician to complete the termination before and during the construction process. Package of 25.



- **Category 6:** Standards compliant.
- **Easy to follow universal wiring label:** Quick and user-friendly, eliminates confusion.
- **Rear loading:** Preferred mounting for panels.
- **Icon compatible:** Supports 606 designation requirements.
- **RoHS compliant:** Lead free.

---

### SPECIFICATIONS

#### GENERAL INFO

Color: Gray  
Footprint: Keystone  
Number Of Ports: 1  
Performance Category: Cat 6 component compliant  
UL Standards Tested: UL 1863  
Product Series: TechChoice  
Type: Jacks and Modules

#### LISTING AGENCIES/THIRD PARTY CERTIFICATIONS

RoHS: Yes  
CUL Listing No: E131600  
UL Listing No: E131600

## **DIMENSIONS**

Depth (Metric): 28.7mm  
Depth (US): 1.13 in  
Height (Metric): 22.3mm  
Height (US): .88 in  
Width (Metric): 16.25mm  
Width (US): .64 in

## **TECHNICAL INFORMATION**

Category Rating: Cat 6 component compliant  
Performance Rating: Cat6

## **BUY AMERICAN ACT COMPLIANCE**

Country Of Origin: CHINA  
Buy American Act Status: Exception  
Note: Contact Customer Support for Buy American Act options