



## MIGHTY MO AIR CURTAIN, HANGING VINYL PANEL, 146"H X 12"L

OR-MMACNP146X12 | [Ortronics](#)

### FEATURES & BENEFITS

**[DISCONTINUED]** Mighty Mo Air Control products significantly reduce cooling requirements by creating a physical separation between the cold and hot air. They provide a contained supply of cold air to equipment, dramatically reducing active equipment energy consumption.

The Air Curtain containment system includes hanging panels, sliding doors and swinging doors – all designed to eliminate the mixing of hot and cold airflow.



- **Fire resistant vinyl panels hang from aluminum tracks mounted to the drop ceiling grid above the racks and cabinets:** This forms a barrier between the hot aisle and cold aisle.
- **The aluminum tracks are connected to the ceiling grid by fusible links that release and drop to the floor when temperatures go above 135°:** Ensures that the fire sprinkler pattern is not interrupted.
- **Sold in kits:** Includes all necessary hangers, track and panels to cover your specific area.
- **The vinyl panels are the length of the aluminum track and overlap at the track seams:** Creates one continuous partition.

To determine the size of the Hanging Vinyl Panel System required you will need the following measurements:

- **Linear feet** – this is the length of aluminum track needed to create a rectangle around the aisle to be contained. Kits are available from 1' to 6' long and can be connected to one another for larger installations.
- **Drop down length (in inches)** – this is the length of the vinyl panels from the aluminum track to the top of the racks and cabinets or floor. Available lengths are from 29" to 182" high.

### SPECIFICATIONS

#### GENERAL INFO

Discontinued: Yes  
Installation Destination: Rack Level

#### LISTING AGENCIES/THIRD PARTY CERTIFICATIONS

RoHS: Yes

## **CONSTRUCTION INFORMATION**

Component 1: Track

Component 2: Curtain

Finish Plating 1: Clear

Material 1: Aluminum

Material 2: Fire resistant clear vinyl

## **DIMENSIONS**

Height (US): 146"

Length (US): 12"

## **BUY AMERICAN ACT COMPLIANCE**

Buy American Act Status: Buy American Act Compliant