
CASSETTE, M4, LC QUAD, 1U, 50 LOMF, T3, 24F, 2MPO(M)

OR-M4LCQ24-50EA3A1 | [Ortronics](#)



FEATURES & BENEFITS

Cassette, M4, LC Quad, 1U, 50 LOMF, T3, 24F, 2MTP(M)



PRODUCT
ENVIRONMENTAL PROFILE

- Compact high density design
- Plunger/grommet fasteners
- Front loading
- Fiber port labeling
- Metal housing
- Internal bend radius limiting feature built-in
- Permanently attached insertion loss test data label

SPECIFICATIONS

GENERAL INFO

Connection Type: MPO
Installation Destination: Fiber Cabinets
Product Series: Infinium
Type: High Density Cassettes

LISTING AGENCIES/THIRD PARTY CERTIFICATIONS

RoHS: Yes

DIMENSIONS

Rack Units: 1

CORD INFORMATION

Fiber Type: 50 LOMF

TECHNICAL INFORMATION

Connection Method: Method A

Fiber Capacity: 24

Typical Insertion Loss: 0.5

Typical Return Loss: 20

Capacity: High Density

Equipment Type: Pre-Terminated Cassettes

BUY AMERICAN ACT COMPLIANCE

Country Of Origin: CHINA