

---

## 12-FIBER OS2 M4 CASSETTE WITH 12 LC DUPLEX ADAPTERS TO 1 MPO (M), TIER 1, METHOD B, FAR END

M4LCD12-09C1B1 | [Legrand](#)



---

### FEATURES & BENEFITS

Infinium M4 pre-terminated cassettes with method B provide rapid deployment and have a flipped polarity inside the modules, which use key-up to key-up MPO adapters and allows for straight through patching. The rugged metal housing offers additional durability and includes a built-in internal bend limiting feature to assure optimum optical performance.



- **Method B connectivity:** Has flipped polarity and uses key-up to key-up adapters.
- **Pre-terminated solution:** For fastest installation, highest performance and consistent factory quality.
- **Fiber port labeling:** Provides easier administration.
- **Compact high density design:** Made with a rugged metal housing.

---

### SPECIFICATIONS

#### GENERAL INFO

Category Performance Application: OS2

Number Of Ports: 12

Typical Applications: Single-mode

Connection Type: MPO-LC

Installation Destination: Fiber Cabinets

Product Series: Infinium

Type: High Density Cassettes

#### LISTING AGENCIES/THIRD PARTY CERTIFICATIONS

RoHS: Yes

#### DIMENSIONS

Depth (US): 4.76"

Height (US): 1.14"

Width (US): 3.45"

**CORD INFORMATION**

Fiber Type: 9/125

**TECHNICAL INFORMATION**

Connection Method: Method B

Fiber Capacity: 12

Capacity: High Density

Equipment Type: Pre-Terminated Cassettes

**BUY AMERICAN ACT COMPLIANCE**

Country Of Origin: CHINA