
M2 SPLICE CASSETTE, 12 FIBER, SC DUPLEX, OM4, TIER 3

M2SCD12-50E3A1S | [Legrand](#)



FEATURES & BENEFITS

This M2 Splice Cassette enables fast, field termination and provides cable management within the housing. The M2 Splice Cassette is designed for use with Multimode OM4 fiber, houses 12 fibers, and provides SC Duplex ports. This cassette supports fusion splicing of individual fibers, with heat shrinks, pigtail slack and cable slack managed within the cassette. This eliminates the need for individual splice trays or housings, as well as allowing splicing to be done away from the rack housing in a suitable workspace as needed. The design of the cassette allows it to be easily mounted from either the front or the rear of an enclosure or panel. Individual fibers within the cassette may be accessed without disturbing the other fibers in the housing. Tier 3 performance characteristics of this cassette produce typical insertions loss of 0.15dB.

- Mounts from either the front or rear of the enclosure or panel
- Manages fibers within the enclosure
- Tier 3 performance characteristics for insertion and return loss

SPECIFICATIONS

GENERAL INFO

Connection Type: SC
Installation Destination: Fiber Cabinets
Product Series: Momentum 2