
ST FIELD TERMINATING, 50/125, 900 MICRON BUFFER, 25 PACK

OR-205KAS9EB-50T | [Ortronics](#)



FEATURES & BENEFITS

Discontinued ST Field Terminating, 50/125, 900 micron buffer, 25 pack. OptiMo 10Gb/s field installable ST connector, for use with 50 micron multimode fiber, is suitable for 10 Gigabit applications.



- Factory produced connector polish
- Factory polish process monitored using advanced laser interferometry
- No polishing required in the field
- No epoxy required
- Unlimited shelf life connector
- 62.5/125, Enhanced 50/125 and single mode options
- Lightweight, convenient Termination Kit

SPECIFICATIONS

GENERAL INFO

Connection Type: ST
Product Series: OptiMo

LISTING AGENCIES/THIRD PARTY CERTIFICATIONS

RoHS: Yes

CORD INFORMATION

Fiber Type: 50/125, Enhanced Bandwidth (10 Gig)
Finish End One: Physical Contact-PC

TECHNICAL INFORMATION

Field Assembly Time: 1 minute on 900 micron buffer, 3 minutes on jacketed cable
Storage Temperature: -40 to + 104 degrees F (-40 to + 40 degrees C)

Typical Insertion Loss: 0.30000001
Typical Return Loss: -30
Equipment Type: Pre-polished Connectors