

---

## LC FIELD TERMINATING, 62.5/125, 900 MICRON BUFFER, 25 PACK

OR-205KAS9GB-62 | [Ortronics](#)



---

### FEATURES & BENEFITS

**Discontinued** LC Field Terminating, 62.5/125, 900 micron buffer, 25 pack. OptiMo field-installable LC connector, for use with 62.5 micron multimode fiber, incorporates a factory-bonded fiber stub, ceramic ferrule, and precise factory polish.



- Factory produced connector polish
- Factory polish process monitored using advanced laser interferometry
- No polishing required in the field
- No epoxy required
- Unlimited shelf life connector
- 62.5/125, Enhanced 50/125 and single mode options
- Lightweight, convenient termination kit

---

### SPECIFICATIONS

#### GENERAL INFO

Connection Type: LC  
Product Series: OptiMo

#### LISTING AGENCIES/THIRD PARTY CERTIFICATIONS

RoHS: Yes

#### CORD INFORMATION

Fiber Type: 62.5/125  
Finish End One: Physical Contact-PC

#### TECHNICAL INFORMATION

Field Assembly Time: 1 minute on 900 micron buffer, 3 minutes on jacketed cable

Storage Temperature: -40 to + 104 degrees F (-40 to + 40 degrees C)

Typical Insertion Loss: 0.30000001

Typical Return Loss: -30

Equipment Type: Pre-polished Connectors