



SC/PC SPLICE-ON CONNECTOR (SOC) FOR 3.0MM FIBER, 50/125 MULTIMODE OM3 - AQUA

205KNF3FA-50T |

FEATURES & BENEFITS

Using a factory-terminated and pre-polished connector, this Splice-On Connector (SOC) provides a connection that meets or exceeds industry standards for loss and back reflection. The Connector is provided with a factory-cleaved 900um fiber stub to ensure ease of use and optimal performance.

The unique boot allows the entire splice to be concealed and protected. The addition of an extended brass crimp sleeve provides extra protection to the splice and utilizes the Kevlar for maximized pull strength. This Splice-On Connector is designed to work with many fusion splicers (cordage fiber holders & Universal SOC Oven are required).

- **Return loss: 35dB.**
- **3mm boot protects splice for easy cable management.**
- **Brass crimp included to protect splice.**

SPECIFICATIONS

GENERAL INFO

Category Performance Application: OM3

Color: Aqua

Typical Applications: Multimode

LISTING AGENCIES/THIRD PARTY CERTIFICATIONS

RoHS: Yes

CORD INFORMATION

Connector Type End One: SC PC

Fiber Type: Multimode

Finish End One: Physical Contact-PC

TECHNICAL INFORMATION

Connector Intermateability End One: IEC 61754-4

Typical Return Loss: 35dB

Equipment Type: Pre-polished Connectors