

---

## HIGH DENSITY, LOW PROFILE, RACK MOUNT FIBER CABINET FOR PATCHING

OR-625MMC-24PG1RB | [Ortronics](#)



---

### FEATURES & BENEFITS

This pre-loaded cabinet secures, protects, and organizes up to 24 single mode optical terminations. The cabinet also provides interconnect or cross connect facilities between horizontal and backbone inside plant (ISP) or outside plant (OSP) cables. Unit supplied pre-loaded with 24 blue SC-Simplex adapters containing ceramic alignment sleeves, suitable for single mode applications. Face recessed, fiber capacity: 24



- Pre-loaded with fiber optic adapters
- Slide-out fiber management drawers
- Includes bend limiters at patch cord exits
- Universal mounting brackets suitable for 19" and 23" installation
- Internal bend limiting clips provided
- 1.5" deep front shelf
- Top panel removable
- Rear door opens with quarter-turn fasteners
- 1.75" openings in the top and bottom
- Smoked, shatterproof plexi door with lock

---

### SPECIFICATIONS

#### GENERAL INFO

Number Of Ports: 24  
Typical Applications: Single-mode  
Installation Destination: Rack Mount  
Product Series: 625 Series

#### ASSEMBLY/INSTALLATION INFORMATION

Mounting Hardware Included: Yes

#### LISTING AGENCIES/THIRD PARTY CERTIFICATIONS

RoHS: Yes

## **DIMENSIONS**

Depth (Metric): 343 mm

Height (Metric): 44 mm

Height (US): 1.75"

Width (Metric): 483 mm

Rack Units: 1

## **TECHNICAL INFORMATION**

Fiber Capacity: 24

Rack (mm): 44

Rack (Inches): 1.75

Capacity: High density

Equipment Type: Fiber Cabinets

## **BUY AMERICAN ACT COMPLIANCE**

Country Of Origin: UNITED STATES OF AMERICA

Buy American Act Status: Buy American Act Compliant

