
2 MM ZIP CORD PREMIUM PERFORMANCE LASER OPTIMIZED (50/125) OM3 LC-PC TO LC-PC OFNR 2M

OR-P3DF2LRGZGZ002M | [Ortronics](#)



FEATURES & BENEFITS

2 mm duplex fiber optic zip cords are available using either 50-micron OM4, 50-micron OM3, or single-mode OS2 fiber. Standard configurations include LC-LC, SC-SC and SC-LC. Duplex zip cords include duplexing clips, either installed at the factory, or unassembled in the bag – your choice.



PRODUCT
ENVIRONMENTAL PROFILE

SPECIFICATIONS

GENERAL INFO

Cable Type: Zip Duplex
Category Performance Application: OM3
Color: Aqua
Typical Applications: Multimode
Product Series: Infinium

LISTING AGENCIES/THIRD PARTY CERTIFICATIONS

RoHS: Yes

DIMENSIONS

Diameter (US): 2.0
Length (Metric): 2

CORD INFORMATION

Connector Type End One: LC
Connector Type End Two: LC
Fiber Type: OM3
Finish End One: Physical Contact-PC

Finish End Two: Physical Contact-PC
Jacket Rating: UL OFNR Riser

TECHNICAL INFORMATION

Performance Rating: Multimode 50125
Equipment Type: Patch Cords

BUY AMERICAN ACT COMPLIANCE

Country Of Origin: TAIWAN
Buy American Act Status: Trade Agreement Act Compliant