


---

## SINGLE MODE PIGTAIL, 12-FIBER, 900 MM, LC-UPC, 2 METERS

OR-P1TC4ZRSZZ002M | [Ortronics](#)



---

### FEATURES & BENEFITS

Ortronics Fiber Assemblies can be ordered in various lengths with any standard connectors and are available either in multimode or single mode fiber with any standard ceramic connector including ST, FC, LC & SC. For lengths, cable types, or connector styles not shown, please consult Ortronics sales at (800) 934-5432. When high density is required, Ortronics recommends the duplex MT-RJ and LC based products. All of Ortronics cables are manufactured to exceed the optical attenuation requirements of TIA/EIA-568-B.3 and are 100% visually inspected. Formally product number OR-626TC4ZR-SZ002M.



- **All common fiber types offered:** Provides industry leading performance and assures compliance to common industry standards.
- **Industry leading guarantee of 0.50 dB or better (versus TIA/EIA 568B.3 requirement of 0.75 dB):** Supports robust low loss fiber optic transmission in structured cabling systems.
- **100% visual inspection:** Ensures that all polished surfaces are free from defects.
- **100% Insertion Loss testing, test report included:** Ensures low loss connections.

---

### SPECIFICATIONS

#### GENERAL INFO

Cable Type: Pigtails  
Typical Applications: Single-mode

#### LISTING AGENCIES/THIRD PARTY CERTIFICATIONS

RoHS: Yes

#### DIMENSIONS

Length (Metric): 2

#### CORD INFORMATION

Connector Type End One: LC-UPC  
Connector Type End Two: Unterminated  
Finish End One: Ultra Physical Contact-UPC  
Finish End Two: Physical Contact-PC  
Jacket Rating: UL OFNR Riser  
Min Bend Radius: 25 mm (1")

#### TECHNICAL INFORMATION

Fiber Capacity: 12  
Performance Rating: Singlemode 9125  
Equipment Type: Patch Cord