
UPS, LINE INTERACTIVE, LCD, 1500VA, 120V, 2U, (8) 5-15R, 5-15P CORD

LU-1500-RTL | [Legrand](#)



FEATURES & BENEFITS

Protect critical hardware in IT closets, data networks, retail, and financial branches through automatic voltage regulation (AVR) to correct voltage irregularities without switching to battery. Multiply the reach and ability of IT staff and caretakers through a single portal, providing visibility and control of power usage and available capacity, simplifying maintenance responsibilities for taxed IT departments.



- **Ultra Low Transfer Time:** Quick transfer of power from AC to battery
- **Automatic Voltage Regulation (AVR):** Corrects voltage irregularities without switching to battery
- **Pure Sinewave Output:** Provides the ideal waveform for the most sensitive equipment
- **Wide Input Voltage Range:** Enables stable wide range application usage
- **Input Power Factor 0.9:** Optimized and ideal efficiency at full load
- **Programmable Outlet Bank:** Power management outlets enable programmable control of load segments to extend battery time to mission critical equipment
- **Optional Remote Management Control:** Provides visibility and control of power usage and availability, both on-site or at a remote unmanned facility
- **4-Post Rack Mounting Kit:** Included for simplified rack mounting
- **Tower Mounting Option:** Includes feet for non-rack applications, enabling the UPS to stand up by providing stability

SPECIFICATIONS

GENERAL INFO

Color: Black
Product Series: LU-Series
Type: Uninterruptible Power Supply
Component Type: Line Interactive UPS
Input Plug Type: NEMA 5-15P

LISTING AGENCIES/THIRD PARTY CERTIFICATIONS

RoHS: Yes

DIMENSIONS

Rack Units: 2

TECHNICAL INFORMATION

AC Voltage Output: 81-145V

Mounting: 19" Rack Mount

Capacity: 1.44kVA

Receptacle Type: 5-15R

Number Of Receptacles: 8

BUY AMERICAN ACT COMPLIANCE

Country Of Origin: CHINA