

---

## UPS, ONLINE, LCD, 3000VA, 120V, 2U, (8) 5-20R & (1) L5-30R, 5-30P CORD

LU-3000-RT | [Legrand](#)



---

### FEATURES & BENEFITS

Protect mission critical hardware in IT closets, voice and data networks, unmanned facilities, light industrial, and financial branches through double-conversion online power protection. Multiply the reach and ability of IT staff and caretakers through a single portal, providing visibility and control of power usage and available capacity, simplifying maintenance responsibilities for taxed IT departments.



- **Zero Transfer Time:** Seamless transfer of power from AC to battery and inverter to bypass
- **True Double-Conversion:** Provides the highest protection from raw input power (surges, spikes, and dips)
- **Pure Sinewave Output:** Provides the ideal waveform for the most sensitive equipment
- **Wide Input Voltage Range:** Enables stable wide range application usage
- **Input Power Factor Correction:** Optimized and ideal efficiency at full load
- **Programmable Outlet Bank:** Ensures efficient and timely powering down of attached non-critical equipment
- **Designed to Work in Tandem with a Generator:** Ensures smooth transition to generators during longer outages
- **Optional Remote Management Control:** Provides visibility and control of power usage and availability, both on-site or at a remote unmanned facility
- **4-Post Rack Mounting Kit:** Included for simplified rack mounting
- **Tower Mounting Option:** Includes feet for non-rack applications, enabling the UPS to stand up by providing stability

---

### SPECIFICATIONS

#### GENERAL INFO

Color: Black  
Product Series: LU-Series  
Type: Uninterruptible Power Supply  
Component Type: Online UPS  
Input Plug Type: NEMA L5-30P

#### LISTING AGENCIES/THIRD PARTY CERTIFICATIONS

RoHS: Yes

## **DIMENSIONS**

Rack Units: 2

## **TECHNICAL INFORMATION**

AC Voltage Output: 80-150V

Mounting: 19" Rack Mount

Capacity: 3kVA

Receptacle Type: 5-20R, L5-30R

Number Of Receptacles: 9

## **BUY AMERICAN ACT COMPLIANCE**

Country Of Origin: CHINA