



18RU, SWING-OUT WALL-MOUNT CABINET, PERFORATED DOOR

SWM18RUPD-26-26 | [Legrand](#)

FEATURES & BENEFITS

The Legrand SWM Series wall mount cabinets provide a convenient and easy to use solution, perfect for secure networks, small data closets, retail, educational, edge computing, and all areas where floor space is limited.

Convenience

The SWM Series wall mount cabinets ship completely assembled which speeds installation time. The hinged, swing out middle section provides easy accessibility to the front and the rear of the equipment while mounted to the wall. The reversible rails can be reconfigured to allow for 12-24 threaded hole mounting or for square hole mounting of equipment, easy to setup and remain adjustable regardless of their orientation — perfect for network or server applications.

Durability

The SWM cabinets are made of rugged welded steel and have a UL 2416 certified load rating of 150 lbs. The small form factor cabinets are PCI compliant, have a 23.5" equipment mounting depth and feature a solid locking door that provides security for the installed equipment.



- Certified load rating of 150 lbs per UL2416
- PCI Compliant
- Full swing handle
- Reversible hinged solid front locking door
- Vented sides with mounting locations for optional cooling fans
- Reversible rails for network or server configurability
- 12-24 threaded and square punched mounting holes
- Cable knockouts at top and bottom of fixed rear pan
- Large cutout in rear pan for access to wall
- 2 reversible mounting rails
- 2 front door lock keys
- 8 cable management rings
- Owner's manual

SPECIFICATIONS

GENERAL INFO

Available Internationally: No

Color: Black

Product Series: SWM

Type: Wall-Mount Cabinets

Component Type: Swing-Out Wall-Mount Cabinet

LISTING AGENCIES/THIRD PARTY CERTIFICATIONS

RoHS: Yes

CONSTRUCTION INFORMATION

Component 2:

Finish Plating 3:

Material 1: Steel

Material 3:

DIMENSIONS

Depth (Metric): 711.20 mm

Depth (US): 28"

Height (Metric): 901.70 mm

Height (US): 35.50"

Width (Metric): 660.40 mm

Width (US): 26.00"

Overall Dimensions (Metric): 901.70 mm H x 660.40 mm W x 711.20 mm D

Overall Dimensions (US): 35.50" H x 26.00" W x 28.00" D

Rack Units: 18

TECHNICAL INFORMATION

Static Load Capacity: 275 lbs

UL Load Capacity: 275 lbs

BUY AMERICAN ACT COMPLIANCE

Country Of Origin: UNITED STATES OF AMERICA

