

4RU SINGLE-SIDED HORIZONTAL CABLE MANAGER - WHITE

SHMC4RU-W | [Legrand](#)



FEATURES & BENEFITS

This Single-Sided Horizontal Cable Management Panel is the perfect solution for managing cables within a rack or cabinet in a wide variety of applications. This panel is designed to mount on any 19in EIA style rack or cabinet, and features a unique finger design that protects cables from damages. The cover mounts with six hinge clips to enable the door to be opened one-handed without becoming unhinged.

The fingers begin 3/4in from the rack face to provide cable bend limitation that protects the cables and equipment – ensuring optimum network performance. This panel includes the necessary mounting hardware, so there are no additional parts to order.



- Material: UL94V-0 rated plastic.
- Dimensions (HxWxD): 6.97x19.03x8.31.

SPECIFICATIONS

GENERAL INFO

Color: White
Product Series: Standard EIA
Type: Organizers
Component Type: Horizontal Cable Manager

ASSEMBLY/INSTALLATION INFORMATION

Mounting Hardware Included: Yes

LISTING AGENCIES/THIRD PARTY CERTIFICATIONS

RoHS: Yes
UL Standard: UL 94V-0

CONSTRUCTION INFORMATION

Material 1: PC/ABS Plastic

DIMENSIONS

Depth (US): 14.25"

Height (US): 1.72"

Width (US): 19"

Height: 1.72"

Rack Units: 1

TECHNICAL INFORMATION

Signal Safe:

- **Available in 1RU and 2RU sizes:**Provides a choice of less rack space or more capacity.
- **Four 12-24 equipment mounting screws provided:** No additional parts to order.
- **Front fingers begin 3/4" from the face of rack to provide bend limitation for cables:**Protects cables, equipment and network performance.
- **Rear fingers are removable (shipped uninstalled):**Allow easy access for lacing and punching down IDC patch panels.
- **Included hinged covers mount with six heavy duty clips:** Can be opened one handed without becoming "unhinged".

BUY AMERICAN ACT COMPLIANCE

Country Of Origin: UNITED STATES OF AMERICA

