



MM20 4-POST RACK, 30"D FIXED, 8'H, 51 RU, TAPPED #12-24

OR-MM20830FXD12-X | [Ortronics](#)

FEATURES & BENEFITS

Mighty Mo 20 4-post racks provide greater flexibility and optimum efficiency in any data center. The fixed racks provide an economical mounting platform for switches and servers while the adjustable rack allows all 4 mounting rails to be adjusted even after the rack has been fastened to the floor. Front and rear waterfalls allow for equipment patching and server patching. All styles of Mighty Mo 20 vertical managers can be mounted front or rear and airflow baffles can be mounted to manage the airflow of side breathing equipment.

Note: Static capacity 2,000 lbs. Assembly required. Replace the "X" tail code with "B" for black or "W" for white.



PRODUCT
ENVIRONMENTAL PROFILE

- **Front profile matches the Mighty Mo 20 channel racks and the rear has an additional waterfall for server cable routing:** Provides a unified, streamlined look throughout the row of racks and allows both styles to share vertical management.
- **The mounting rails adjust from 12.5" to 36" or 42" depending on rack size, independent of the structural members:** Allows the rails to be adjusted after the rack is installed.
- **Choice of vertical management can be mounted front or rear:** A solution for every application; vertical cable management cage with individual rack unit fingers and hinged slam latch door, vertical cage with individual rack unit fingers and snap on covers, vertical cage with hinged latches, and individual cable management rings.
- **Built-in top trough with waterfalls:** Front and rear gives bend radius control and cable routing.
- **Rack includes two packages of hook and loop D-style straps and 50 #12-24 screws:** Do not have to purchase as separate items; money saving.

SPECIFICATIONS

GENERAL INFO

Color: (B)lack or (W)hite

Product Series: Mighty Mo 20

Type: Cable Management Racks

Component Type: 4-Post Rack

ASSEMBLY/INSTALLATION INFORMATION

Assembly Required: Yes

Mounting Hardware Included: Yes

LISTING AGENCIES/THIRD PARTY CERTIFICATIONS

RoHS: Yes

CONSTRUCTION INFORMATION

Component 1: 4-Post Rack

DIMENSIONS

Capacity Weight (US): 2000 lbs

Depth (US): 40

Diameter (Metric):

Height (Metric): 2.4892 m

Height (US): 98"

Length (Metric):

Width (Metric): 603.25 mm

Width (US): 23.75"

Height: 98"

Rack Units: 51

TECHNICAL INFORMATION

Static Load Capacity: 2,000 lb

Patent No: 8,130,494 and 8,256,181

BUY AMERICAN ACT COMPLIANCE

Country Of Origin: UNITED STATES OF AMERICA

Buy American Act Status: Buy American Act Compliant

