



MM6 VERTICAL CABLE MANAGEMENT CAGE WITH DUAL HINGED COVERS, 4" X 7" X 8'

OR-MM6VMS804 | [Ortronics](#)

FEATURES & BENEFITS

MM6 Vertical Cable Management Cage with dual hinged covers, 4" x 7" x 8', black



- **Vertical cage with individual rack unit fingers has a fill capacity of 150 Category 6 patch cords and 105 10Gig patch cords:** Provides organized method for routing and storage of patch or cross connect cable between racks.
- **Dual snap on hinged covers:** The door allows easy access during moves, adds and changes.
- **Mounted on the front flange between the Mighty Mo 6 racks when two or more are installed in a row, on a single rack or the end of a row:** Creates a 2-1/2" channel between racks for front to back routing of equipment cables and patch cords.
- **Supplied with four slack storage spools and 12 bend limiting clips:** Adjustable bend limiting control for copper and fiber cords.
- **All necessary mounting hardware included:** Hanger clips hold the cage in place for easy and quick one person installation.

SPECIFICATIONS

GENERAL INFO

Product Series: Mighty Mo 6

Type: Vertical Managers

Component Type: Vertical Manager with Cover

LISTING AGENCIES/THIRD PARTY CERTIFICATIONS

RoHS: Yes

CONSTRUCTION INFORMATION

Component 1: Vertical management cage

Component 2: Cover

Component 3: Clip, finger

Component 4: Cable management finger sections

Component 5: Bracket, end mount

Finish Plating 1: Powercoat black

Finish Plating 2: Medium texture black

Finish Plating 3: Black
Finish Plating 4: Black
Finish Plating 5: Painted black
Material 1: .875 Wire
Material 2: .060 Aluminum
Material 3: polycarbonate
Material 4: Polycarbonate
Material 5: 16 AWG (.060) Cold rolled steel

DIMENSIONS

Depth (Metric): 165.6 mm
Height (Metric): 2.67 m
Height (US): 87.44"
Width (Metric): 96 mm
Rack Units: 0

TECHNICAL INFORMATION

Patent No: 6,946,605 7,026,553

BUY AMERICAN ACT COMPLIANCE

Country Of Origin: UNITED STATES OF AMERICA
Buy American Act Status: Buy American Act Compliant

